Document No. 149-964 July 30, 2014

# ATEC Base VAV Controller & ATEC VAV Reheat Controller



## Description

The ATEC (Actuating Terminal Equipment Controller) Variable Air Volume Controllers provides high performance direct digital control (DDC) of pressure-independent, variable-air-volume zone-level routines. The ATEC controllers can operate stand-alone or can be networked to perform complex HVAC control, monitoring and energy management functions. The ATEC controllers are designed to reside on any Siemens control system.

#### **Features**

- Controller integrated with actuator for ease of installation.
- Automated checkout procedure for ease of startup/commissioning and troubleshooting.
- PID control of HVAC systems to minimize offset and maintain tighter set point control.
- HVAC diagnostic capability at the BLN level using the TBC Test Tool in CT 4.8.

- ATEC Base VAV Controller requires only 3.5 VA, an advantage when sizing electrical capacity.
- Plenum rated controller.
- Setpoints and control parameters assigned and changed locally or remotely.
- Setpoints and control parameters stored in Electrically Erasable Programmable Read Only Memory (EEPROM)—no battery backup required.
- Return from power failure without operator intervention.
- No calibration required, thereby reducing maintenance costs.

# **Applications**

Operating independently, or as part Siemens APOGEE System, the ATEC VAV Controller can control the following VAV pressure- independent zone applications.

#### **ATEC Base VAV Controller:**

- VAV Cooling Only (Application 2520—similar to 2020 for the ATEC)
- VAV Cooling or Heating (Application 2521 similar 2021)
- Slave Mode (Application 2486)

#### **ATEC VAV with Reheat Controller:**

- VAV Cooling Only (Application 2500—similar to 2020)
- VAV Cooling or Heating (Application 2501 similar to 2021)
- VAV with Electric Reheat or Baseboard Radiation (Application 2522—similar to 2022)

Document No. 149-964 Page 1 of 3

- VAV with Hot Water Reheat (only one reheat valve) (Application 2523—similar to 2023 with one reheat valve)
- VAV Series Fan Powered with one stage of Electric Reheat (Application 2524—similar to 2024 with one stage of electric reheat)
- VAV Parallel Fan Powered with one stage of Electric Reheat (Application 2526—similar to 2026 with one stage of electric reheat)
- Slave Mode (Application 2473)

Control algorithms are preprogrammed. The controller is ready to operate after selecting the application and assigning the unit's controller address. If desired, the operator may adjust the air volume set points in cfm (I/s), room temperature set points, and other parameters.

#### Hardware

#### **Controller Board**

The ATEC consists of an electronic controller, a differential pressure transducer, and a damper actuator assembly. This controller provides all wiring terminations for system and local communication and power. The cable from the room sensor (purchased separately) connects to an RJ-11 jack on the controller. All other connections are removable terminal blocks.

The ATEC Base VAV Controller has no external, wireable I/O. The ATEC VAV with Reheat Controller, however, has additional I/O: 2 AI/DIs and 2 DOs.

In addition to controlling the integrated damper actuator, the controller interfaces with the following external devices (purchased separately):

- Averaging air velocity sensor provided by VAV terminal unit manufacturers.
- Room temperature sensor with optional set point dial and night override button.
- Service and commissioning tools.

#### **Room Sensor**

The room sensor connection to the controller board consists of a quick-connect RJ-11 jack. This streamlines the installation and reduces controller start-up time. See the *Room Temperature Sensors Technical Specification Sheet* (149-312P25) for more information.

#### **Differential Pressure Sensor**

The Differential Pressure Sensor (purchased separately) is easily connected to the box's airvelocity sensing elements to provide measurement of the differential pressure. The measured value is converted to actual airflow in cfm (I/s) by the ATEC controller.

### **ATEC Specifications**

| Controller & Actuator  |  | _                                     |
|--|--|---------------------------------------|
| Power Requirements: Power Source Frequency   | Base:<br>24 Vac +/-<br>15%<br>50/60 Hz                           | Reheat:<br>24 Vac +/- 15%<br>50/60 Hz |
| Power Consumption  | 3.5 VA   | 3.5 VA plus loads                     |
| Operating Temperature Range  | +32°F to 122°F<br>(0°C to 50°C)                                  |                                       |
| Shipping & Storage<br>Temperature Range  | -13°F to 158°F<br>(-22°C to 70°C)                                |                                       |
| Humidity Range   | 5 to 95% rh (non-condensing)                                     |                                       |
| Regulatory Compliance  | UL/CUL 916 PAZX/PAZX7<br>(Enclosed Energy<br>Management)         |                                       |
|  | FCC Part 15, Class B<br>CSA-Std. C22.2 No 205<br>CE Mark; C-Tick |                                       |
| Dimensions   | ,  | 15/16"W x 4-3/16"D<br>'5 mm x 106 mm) |
| Weight   | 1.26 lbs (.57  | '2 kg)                                |
| Actuator Torque  | 44 lbin. (5N   | lm)                                   |
| Run time for 90°<br>opening or closing at:<br>50 Hz<br>60 Hz<br>Nom. Angle of Rotation | 108 sec.<br>90 sec.<br>90°                                       |                                       |
| Max. Angle of Rotation   | 95°  |                                       |
| Actuator Shaft Size  | 3/8" to 5/8" (   | 8 to 16 mm) Dial                      |
|  | 1/4" to 1/2" (   | 6 to 13 mm) Sq.                       |
| Minimum Shaft Length   | 3/4" (20 mm  | )                                     |

# Transformer Requirements and Recommended Voltages

| Type | Class 2, 24 VAC, 50/60 Hz, SELV, PELV   |
|------|---|
| туре | 01833 2, 24 VAC, 30/00 112, 3LLV, 1 LLV |

Page 2 of 3 Siemens Industry, Inc.

# **Product Ordering Information**

| Descri  | ption  | Product<br>Part<br>Number |
|---------|--|---------------------------|
| ATEC E  | Base VAV Controller  | 550-400                   |
| ATEC E  | Base VAV Controller—10 pack                                      | 550-400P10                |
| 1 RS    | Tool/10 K $\Omega$ Thermistor Room Sensor Module Connection Port |                           |
| ATEC \  | /AV with Reheat Controller                                       | 550-405                   |
| ATEC \  | /AV with Reheat Controller—10 pack                               | 550-405P10                |
| 2 AI/DI | 100 K $\Omega$ Thermistor or Dry Contact                         |                           |
| 2 DO    | 12 VA, 24 Vac Triac  |                           |
| 1 RS    | Tool/10 K $\Omega$ Thermistor Room Sensor Module Connection Port |                           |

# **Documentation Information**

| Specification Sheet/Application Bulletin               | Product<br>Part<br>Number |
|--|---------------------------|
| ATEC Owner's Manual                                    | 125-3209                  |
| Room Temperature Sensors Technical Specification Sheet | 149-312P25                |

Information in this document is based on specifications believed correct at the time of publication. The right is reserved to make changes as design improvements are introduced. Product or company names mentioned herein may be the trademarks of their respective owners. © 2014 Siemens Industry, Inc.